



APPLICATIONS: Use model 2601 whenever a full extension, very low profile slide is required. Ideal for use in tool boxes, laboratory furniture, and store fixtures. Not suitable for flat mounting. **This product is covered by U.S. (6,254,209) and various foreign patents issued and/or pending.**

Full Extension, Hold-In Detent
Very Low Profile
Up to 75-lb. [34 kg] Capacity**



- ① This mounting hole is **not** accessible on model 2601-12 [300mm].
- ② This mounting slot is **only** available on model 2601-16 [400mm].
- ③ This mounting slot is **not** accessible on model 2601-16 [400mm].



Finish	Bright electro-zinc plating (C) or black zinc (CB) finish available	Side Space	.50" +.030/ -.000 [12.7mm +0.8/ -0.0]
Lengths	Even lengths from 8" to 22" [200mm to 550mm]	Mounting	Side
Travel	Full extension	Hardware	#6 truss head screw
Height	1.03" [26.3mm]	Movement	Steel ball bearings
Load Rating	See chart	Features	Hold-in detent, silenced movement in and out


** Load rating based on a 16" wide drawer cycled 10,000 times.

Part Number	Slide Length	Slide Travel	Load Rating lb [kg]/pair **	A	B	C	D	E
2601-8	7.87 [200]	8.23 [209]	35 lb [16 kg]	5.04 [128.0]				
2601-10	9.84 [250]	10.20 [259]	50 lb [23 kg]	5.04 [128.0]				
2601-12	11.81 [300]	12.13 [308]	70 lb [32 kg]	5.04 [128.0]	8.82 [224.0]			
2601-14	13.78 [350]	14.06 [357]	75 lb [34 kg]	5.04 [128.0]	8.82 [224.0]			
2601-16	15.75 [400]	15.98 [406]	70 lb [32 kg]	5.04 [128.0]	8.82 [224.0]	12.60 [320.0]		
2601-18	17.72 [450]	17.95 [456]	65 lb [30 kg]	5.04 [128.0]	8.82 [224.0]	13.86 [352.0]		
2601-20	19.69 [500]	19.88 [505]	63 lb [29 kg]	5.04 [128.0]	8.82 [224.0]	13.86 [352.0]	16.38 [416.0]	
2601-22	21.65 [550]	21.81 [554]	60 lb [27 kg]	5.04 [128.0]	8.82 [224.0]	13.86 [352.0]	17.64 [448.0]	19.25 [489.0]

Installation Instructions

Install the Cabinet Member

1. Mark a horizontal line in the cabinet sidewall at least 5/8" [15.9mm] above the cabinet floor or at least 5/8" [15.9mm] below the top of the drawer side. Mark a point on the line 2-3/8" [60.2mm] in from the cabinet front. This will position the slide flush with the cabinet opening. For inset drawers, add the drawer front thickness to the 2-3/8" [60.2mm] dimension. See Figure 1.



2. Measure the distance between the front and rear horizontal slots on the slide. Mark this measurement on the horizontal line beginning at the first mark.
3. Install #6 truss head screw through the front and rear horizontal slots. Adjust for horizontal position.
4. Install screws in round holes, front and rear of cabinet member. For longer slides (18" [450mm] and over), install additional screws in the central holes.

Install the Drawer Member

1. Mark a horizontal line on the drawer side in line with the slide center line.
2. Mark a point on the line 2-1/2" [63.5mm] back from the drawer front. Measure the distance between the front and rear horizontal slots on the slide. Mark this measurement on the horizontal line beginning at the first mark.
3. Install a screw through the first horizontal slot. See Figure 1.
4. Install screw and adjust location of drawer.
5. Install screws in the round holes, front and rear of drawer member. For longer slides (18" [450mm] and over), install additional screws in the central holes.

NOTE: To access the additional mounting holes in the cabinet and drawer members of the slide, it is necessary to move the intermediate member to line up the access hole and the mounting hole.

Slide Ordering Instructions

Complete your slide order for model 2601 by specifying the following:

200 Pair C 2601 -18 D

Total Slides Required _____
Slide Finish _____
Slide Model _____
Slide Length _____
Optional Polybag Packaging _____

Packaging

Distributor (D) Pack: All lengths are packaged 10 pair per box. Polybag includes one pair of slides and installation sheet.

Bulk (P) Pack: All lengths are packaged 15 pair per box.

Specifications

Slide members: Cold rolled steel
Ball retainers: Cold rolled steel
Ball bearings: Carburized steel
RoHs Compliant

Note: Specifications, materials, prices, terms, and delivery are subject to change without notice.

Accuride

ACCURIDE INTERNATIONAL INC.

12311 Shoemaker Avenue
Santa Fe Springs, CA 90670

TEL (562) 903-0200
FAX (562) 903-0208

www accuride.com

Manufacturing, Engineering, and Sales

United States • Germany • Japan • Mexico • United Kingdom • China